

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Stainless Steel Flange.

By Hubbell Wiring Device-Kellems
Catalog # [HBL7486](#)

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Screw Terminal, Stainless Steel Flange.



Application

Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL7486
Color	Black, Stainless
Cord Range	0.220"-0.385"(5.6-9.8)
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Flanged Inlet
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Base - Phenolic • Blades - Brass • Flange - Stainless Steel • Terminal Screws - #5-40 Brass

Temperature Rating

Maximum Continuous: 75° C;
Minimum Continuous: -40° C
w/o impact, -25° with impact.

Type UPC

Flanged Inlet
783585237442

Dimensions

Dimensions	2.06 in x 1.63 in x 0.98 in
Display Size	Midget Locking
Height	0.98 in
Length	2.06 in
Weight	0.05 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

Certifications And Compliance

Industry Standard(s)	Listed to UL 498
Nema Rating	ML-3P

Logistics

Carton Quantity	10
Pallet Quantity	5000

Product Assets



A Hubbell brand