

## Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15R, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7506C](#)

Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 125V , 2-Pole 2-Wire Non-Grounding, NEMA L1-15R, Screw Terminal, Black and White Nylon.



### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

### General

Catalog Number	HBL7506C
Color	Black, White
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Non-Grounding Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Assembly Screws - Steel - nickel plated</li><li>• Contacts - Brass</li><li>• Housing / Cord Clamp - Nylon</li><li>• Terminal Clamp - Cold rolled steel - nickel plated</li><li>• Terminal Retainer - Clear polycarbonate</li></ul>

Temperature Rating

Type  
UPC

### Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard
Height	2.78 in
Length	1.53 in
Weight	0.15 lb
Width	1.53 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

### Conductor Related

Cable Range	0.220 - 0.720 in
Number Of Wires	2-Wire
Wire Size	#18 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2 No. 42</li><li>• Fed. Spec W-C-596</li><li>• Listed to UL 498</li></ul>
----------------------	----------------------------------------------------------------------------------------------------------------------------------------

- Terminal Screws - #8-32 Brass (Phillips / Slotted / Robertson)
- Maximum Continuous: 75° C;  
Minimum Continuous: -40° C w/o impact, -25° with impact.
- Connector Body  
783585177908

Nema Rating L6-15R  
Standards - RoHS Compliance CM  
Status

Pallet Quantity 3600

**Product Assets**

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL7506C](#)  
[Warranty - Industrial & Commercial Products](#)

**Logistics**

Carton Quantity 10



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL7506C-SPEC-EN | REV 10/2024