

**HUBBELL**  
Wiring Device-Kellems

**Locking Devices, Twist-Lock®,  
Industrial, Female Connector Body,  
10A 250V/15A 125V, 3-Pole 3-Wire  
Non Grounding, Non-NEMA, Screw  
Terminal and White**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7565C](#)

Locking Devices, Twist-Lock®, Industrial, Female Insulgrip®  
Connector Body, 10A 250V/15A 125V, 3-Pole 3-Wire Non  
Grounding, Non-NEMA, Screw Terminal, Black and White Nylon.



## General

Application	
Catalog Number	HBL7565C
Color	
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	10A/15A Non-Grounding Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact Electrical - Current Interrupting - Certified for current interrupting at full rated current
Performance	Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded copper wire only. Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body Connector Body
UPC	783585178608

## Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard
Height	2.78 in
Length	1.53 in
Weight	0.2 lb
Width	1.53 in

## Electrical Ratings

Amperage Rating	10/15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	10/15 A
Current Rating	10 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250/125 V
Voltage Rating Description	250/125 V

## Conductor Related

Cable Range	0.230 - 0.720 in
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA C22.2 No.42 Fed.Spec. W-C-596 Listed to UL 498
----------------------	---

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Carton Quantity	10
Pallet Quantity	6600

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL7565C-SPEC-EN | REV 6/2024