



Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1) 50A Twist-Lock® Opening, Standard Size, Yellow Polycarbonate

By Hubbell Wiring Device-Kellems
Catalog # [HBL77CM74WO](#)



Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1) 50A Twist-Lock® Opening, Standard Size, Yellow Polycarbonate

Features

- Corrosion resistant, yellow thermoplastic

Application

All 50A Twist-Lock®

General

Construction	Molded
EU RoHS Indicator	Yes
Item Type	Weatherproofing Covers
Knockouts	None
Material - Mounting Hardware	Vertical FS/FD Mount-Mounting Screws
Number Of Outlets	1-Device
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Style	For 50A Twist-Lock® Single Receptacle
Type	<ul style="list-style-type: none">• Covers• Covers
UPC	783585809472

Dimensions

Dimensions	4.56 in x 2.43 in x 3.28 in
Height	3.28 in
Length	4.56 in
Weight	0.40 lb
Width	2.43 in

Electrical Ratings

Dielectric Strength	Withstands 2,000V minimum
---------------------	---------------------------

Certifications and Compliance

Industry Standard(s)	UL Listed - Canadian and U.S.
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL77CM74WO-SPEC-EN | REV 1/2024