

## **Straight Blade Devices, Receptacles, Surface Mounted Single, Industrial Grade, 3-Pole 3- Wire Non-Grounding, 50A 125/250V, 10-50R, Black, Single Pack**



By Hubbell Wiring Device-Kellems  
Catalog # [HBL7940](#)

Straight Blade Devices, Receptacles, Surface Mounted Single,  
Industrial Grade, 3-Pole 3-Wire Non-Grounding, 50A 125/250V,  
10-50R, Black, Single Pack.

### **Application**

Heavy Duty

### **Performance**

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### **General**

Catalog Number	HBL7940
Color	Black
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Brass - Box Terminals</li><li>• Brass - Ground Shunt</li><li>• Housing - Phenolic</li><li>• Mounting Plate - .062 in. (1.5) Pre-Plated Steel</li></ul>

Style	Non-Grounding
Type	Receptacle
UPC	783585015392

### **Dimensions**

Dimensions	5.06 in x 2.5 in x 2.06 in
Display Size	Standard Sized Product
Height	2.06 in
Length	5.06 in
Weight	0.9 lb
Width	2.5 in

### **Electrical Ratings**

Amperage Rating	50 A
Connectivity	Back and Side Wired
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125 V;250 V
Wattage	12500 W

### **Conductor Related**

Number Of Wires	3-Wire
Wire Size	#12 AWG to #4 AWG

### **Certifications And Compliance**

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL Listed File E2186</li></ul>
Nema Rating	10-50R

### **Logistics**

Carton Quantity	10
-----------------	----



A Hubbell brand