

Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15R, White, Bulk Packed

By Hubbell Wiring Device-Kellems
Catalog # [HBL8200HW](#)

Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15R, White, Bulk Packed.

Application

- Slender/Compact Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL8200HW
Color	Blanc
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hospital Grade
Specifications	<ul style="list-style-type: none"> • Automatic Self-grounding Staple - Stainless steel • Base - PBT • Clamping Plate - Nickel plated steel • Contacts - 0.031" (0.8) Brass • Face - PBT



Style
Type
UPC

- Ground Contacts - .031 in. (.8) Brass
 - Mounting Screws - Zinc plated steel
 - Mounting Strap - .050 in. (1.3) Galvanized steel
 - Terminal Screws - Brass
- Finder Groove Face
Receptacle
783585016207

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Slender/Compact
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)

- CSA Certified, C22.2, No. 42 File 285
- Fed. Spec. W-C-596
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating

5-15R

Standards - RoHS Compliance

CM

Status

Logistics

Carton Quantity

10

Pallet Quantity

3600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL8200HW](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL8200HW-SPEC-EN | REV 10/2024