

## Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory, Illuminated Face

By Hubbell Wiring Device-Kellems  
Catalog # [HBL8200ILI](#)

Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory, Illuminated Face.

### Application

Extra Heavy Duty Hospital Grade

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL8200ILI
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hospital Grade
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Clip - .050 in. (1.3) Nickel plated brass</li><li>• Base - PBT</li><li>• By-Pass Power Contacts - .036". (.9) Nickel plated brass</li><li>• Clamp - Nickel plated steel</li></ul>



Style  
Type  
UPC

- Face - Polycarbonate
  - Ground Contacts - .031 in. (.8) Brass
  - Mounting Screws - Stainless Steel
  - Mounting Strap - Brass
  - Terminal Screws - Brass
- Finder Groove Face  
Receptacle  
783585016450

### Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.2 lb
Width	1.33 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2, No. 42 File 285</li></ul>
----------------------	---

- Fed. Spec. W-C-596
  - NEMA® WD-6 Compliant
  - UL Listed to UL498 File No. E2186
- 5-15R

Carton Quantity 10

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL8200ILI](#)  
[Warranty - Industrial & Commercial Products](#)

Nema Rating

### Logistics



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL8200ILI-SPEC-EN | REV 1/2025