

## Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 50A 125V, 5-50R, Black, Single Pack.

By Hubbell Wiring Device-Kellems  
Catalog # [HBL9360](#)



Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 50A 125V, 5-50R, Black, Single Pack.

### Application

Heavy Duty

### Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-0
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### General

Catalog Number	HBL9360
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single Receptacle
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Brass - Box Terminals</li><li>• Brass - Ground Shunt</li><li>• Housing - Reinforced Thermoplastic Polyester</li><li>• Mounting Plate - .062 in. (1.5) Pre-Plated Steel</li></ul>
Type	Receptacle
UPC	783585015262

### Dimensions

Dimensions	3.28 in x 2.25 in x 2.23 in
Display Size	Standard Sized Product
Height	2.23 in
Length	3.28 in
Weight	0.45 lb
Width	2.25 in

### Electrical Ratings

Amperage Rating	50 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	6250 W

### Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #4 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed File E2186</li></ul>
Nema Rating	5-50R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	2560

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL9360](#)



**A Hubbell brand**