

# Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, For 30A Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3RS](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, For 30A Black.

## Features

- Industrial Grade
- Disconnect Switches
- Replacement Switch
- Three Pole

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current voltage
- Electrical - Dielectric Voltage - Withstands 3,000V Min
- Electrical - Max. Working Voltage - 600V RMS
- Electrical - Operations - Mechanical 10,000 cycles
- Electrical 6,000 cycles
- Environmental - Flammability - Meets UL 94V0 material classification
- Environmental - Moisture Resistance - IP66 suitability
- Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C
- Environmental - UV Resistance - All exposed materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External full adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA

## General

Catalog Number	HBLDS3RS
EU RoHS Indicator	No
Item Type	Mechanical Interlock Replacement Switch

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused;Fused
Style	Replacement Switches
Type	Accessories
UPC	783585955179

## Dimensions

Weight	0.4 lb
--------	--------

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3,000V minimum

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating</li> <li>• Listed to UL Standard</li> </ul>
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	20
Pallet Quantity	2000

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - HBLDS3RS](#)
- [Warranty - Industrial & Commercial Products](#)