

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Corrosion Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Side Wired, Orange.

By Hubbell Wiring Device-Kellems
Catalog # IG20CR

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
Corrosion Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,
Side Wired, Orange.



Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG20CR
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Galvanized Steel• Mounting Strap - .040 in. (1) Galvanized steel

- Power Contacts - .030 in. (.8) Brass
 - Terminal Screws - Plated steel
 - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Style
Type
UPC
- Smooth Face
Standard Duplex
783585147628

Dimensions

Dimensions	1.32 in x 1.06 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.32 in
Weight	0.15 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2, No. 42• Fed. Spec. W-C-596
----------------------	---

- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Pallet Quantity 9000

Nema Rating 5-20R
Standards - RoHS Compliance Status CM

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Specifications - IG20CR](#)
- [Warranty - Industrial & Commercial Products](#)

Logistics

Carton Quantity 10



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-IG20CR-SPEC-EN | REV 10/2024