



# Locking Devices, Twist-Lock®, Isolated Ground Industrial, Flush Receptacle, 20A 250V, 2-Pole 3- Wire Grounding, L6-20R, Screw Terminal, Orange

By Hubbell Wiring Device-Kellems  
Catalog # [IG2320](#)



Twist-Lock® Devices, Single Flush Receptacle 20A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-20R, Isolated ground, nylon, Orange

## Features

- Insulation barrier construction isolates ground contact from mounting strap
- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- High-impact, abuse-resistant nylon face
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• Orange</li> <li>• Orange</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	20A Single Flush Receptacle
Listings	<ul style="list-style-type: none"> <li>• UL 498</li> <li>• Fed.Spec. W-C-596</li> <li>• CSA C22.2 No.42</li> </ul>
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical-Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Mechanical - Terminal Accommodation - #16 - #8 AWG solid or stranded copper wire</li> </ul>

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Weight	0.25 lb
Width	1.70 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Mechanical - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

UPC

783585872223



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-IG2320-SPEC-EN | REV 1/2024