

Locking Devices, Twist-Lock®, Isolated Ground Industrial, Flush Receptacle, 30A 3-Phase Wye 120/208V AC, L21-230R, Screw Terminal

By Hubbell Wiring Device-Kellems
Catalog # IG2810



Twist-Lock® Devices, Single Flush Receptacle 30A, 3 Phase Y
120/208V AC, 4 Pole, 5 Wire Grounding, NEMA L21-30R, Isolated
ground, nylon, Orange

Application

Heavy Duty Industrial

Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #16 - #8 AWG solid or stranded copper wire
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Mechanical - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

General

Catalog Number	IG2810
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	3
Item Type	30A Single Flush Receptacle
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - RTP• Contacts - Brass• Face - Nylon• Mounting Strap - Brass

UPC

- Terminal Screws - #10 - 32 Brass
- 783585872506

Dimensions

Dimensions	3.28 in x 1.67 in x 1.31 in
Display Size	Standard Sized Product
Height	1.31 in
Length	3.28 in
Weight	0.3 lb
Width	1.67 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	3 Phase WYE
Voltage Rating	<ul style="list-style-type: none">• 120 V V• 208 V V
Voltage Rating Description	120/208 V

Conductor Related

Number Of Wires	5-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Nema Rating	21-30R

Logistics

Carton Quantity	10
-----------------	----



A Hubbell brand