

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Isolated Ground, 4-Plex, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # IG415

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Isolated Ground, 4-Plex, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack.



Application

Commercial Grade

Performance

- Electrical - Current Interrupting - Capable of withstanding a fault level of 1000A, per UL498
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-12 AWG stranded or solid copper conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG415
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Indicator(s) Type	LED Only
Item Type	Quad Receptacle
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	4-Outlet Receptacle
Specifications	<ul style="list-style-type: none"> • Base - PBT • Face - Polycarbonate • Ground Contacts - .031 in. (.8) Brass • Ground Plate - .032 in. (.8) Plated Steel

Type
UPC

- Power Contacts - .032 in. (.8) Brass
- 4- Plex Receptacle
783585422251

Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard Sized Product
Height	4.3 in
Length	4.3 in
Weight	0.4 lb
Width	0.92 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Listed to UL Standard 498 File E2186 • NEMA® WD-6 Compliant
Nema Rating	5-15R

Logistics

Product Assets



A Hubbell brand