

Surge Protective Devices, SPIKESHIELD IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Blue

By Hubbell Wiring Device-Kellems
Catalog # IG5262SA



Surge Protective Devices, SPIKESHIELD IG TVSS Duplex
Receptacle with Light and Alarm, 15A 125V, 5-15R, Blue

Application

- Decorator Duplex with Light and Alarm

Performance

- Electrical - Protection Modes - Normal and Common Modes
- Electrical - Response Time - Approximately 5 ns
- Electrical - Transient Suppression - Peak Energy (10 X 100 Qs), Peak Current (8 X 20 Qs)
- Electrical - Voltage - 120V AC + 10% - 15%
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

General

Catalog Number	IG5262SA
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Specification Grade
Specifications	<ul style="list-style-type: none">• Base Material - Nylon• Contact Design - Tandem Modified Bypass• Face Material - Nylon• Mounting Strap - .050" (1.3) Steel-Zinc Coated

Style	• Power Contact - .031" (.8) Brass
Type	Isolated Ground Duplex
UPC	783585060699

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified to Specification C22.2 No. 42• Listed to UL Standards 498• UL Listed File E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - IG5262SA](#)
[Warranty - Industrial & Commercial Products](#)