

Ground Fault Products
Heavy Duty Commercial Weather Resistant
GFCI Receptacles

HUBBELL

Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Protects against line and load reversal, no power to the face or downstream if device is miswired
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

Ordering Information

Description	Color	UPC	Catalog Number
20A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, weather resistant, flush face, back and side wired, tri-drive screws	Light Almond	883778999819	GFRWR20LA



Listings

UL Listed - Canadian and U.S.
UL 943 Class A for GFCIs UL File E41978
Meets ADA Standards
Meets all NEC® and CEC requirements
CSA Certified
NEMA® WD-6 ANSI 73 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel
Auto-Ground Staple	Stainless steel

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Frequency	60 Hz
Voltage	120V AC +10% - 15% (102V to 132V)
Amperage	15A/20A, 20A Feed Thru
Maximum Interrupting Capacity	10,000A

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

Accessories

Wallplates for duplex openings	
Solid Right Angle Pigtailed Terminal	SNAP1RA
Stranded Right Angle Pigtailed Terminal	SNAP2RA

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

