

HUBBELL
Wiring Device-Kellems

**Heavy Duty Products, Insulgrip Pin
and Sleeve Devices, Industrial
Grade, Back Box, For 60A 1 1/2"
NPT Hub, Angled, Mounting
Screws Included**

By Hubbell Wiring Device-Kellems
Catalog # [MB603W](#)

Heavy Duty Insulgrip Pin and Sleeve Devices, Industrial Grade,
Back Box, for 60A 1½" NPT Hub, Angled, Mounting Screws
Included



General

Application	Metallic
Catalog Number	MB603W
Color	
Construction	Cast
EU RoHS Indicator	Yes
Item Type	Mounting Box
Knockouts	1 1/2" NPT Hub
Material	Aluminum
Material - Mounting Hardware	Mounting Screws
Number Of Outlets	Accepts 1-Device
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 3,000V AC Electrical - Max Working Voltage - 600V AC RMS Environmental - Flammability - UL94-5VA and V-0 classification Environmental - Operating Temperatures - Max. Continuous: 75° C Min. Continuous: -40° C w/o impact Mechanical - Impact Resistance - In accordance with UL746C Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions
Series	Back Boxes and Adapters
Style	15 Degree
Temperature Range	Limited By Device
Type	Angled Back Box
UPC	783585010762

Dimensions

Display Size	For 60 Amp Devices
--------------	--------------------

Conductor Related

Cable Entry	Through Hub
-------------	-------------

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand