

Kellems Wire Management, Cord Connectors, 90 Degree Male .13-.19", 1/2", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [NHC1020](#)



Kellems Wire Management, Cord Connectors, 90 Degree Male
.13-.19", 1/2", Aluminum

Application

90 Degree Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

| | |
|-------------------------------------|--|
| Catalog Number | NHC1020 |
| Color Code | Orange |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting. |
| Item Type | Cord Connectors |
| Material | Aluminum |
| Material - Mounting Hardware Series | Locknut or Tapped Opening Standard Duty |
| Specifications | <ul style="list-style-type: none">• Cord Diameter Inches (mm) - .13"-.19" (3.2-4.7)• Form Size - F2• Material - Aluminum• NPT Hub Size - 1/2 Inch |

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

90° Male
783585201207

Dimensions

Display Size
Hub Size

1/2" NPT
1/2 "

Conductor Related

Conductor Range
Number of Conductors

0.13-0 .19 in (3.2- 4.7 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating
Standards - RoHS Compliance Status

UL Listed
NEMA Type 4, 4X, 12 and 13
CM

Logistics

Carton Quantity

25

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - NHC1020](#)
[Warranty - Industrial & Commercial Products](#)