

Industrial Grade, Lever Actuated, Switched Enclosure With Receptacle, Three Pole, 30A Hubbellock, 3 Phase 600V AC, Terminal Screws

By Hubbell Wiring Device-Kellems
Catalog # [SEHBL3](#)



Switches and Lighting Controls, Industrial Grade, Lever Actuated, Switched Enclosure With Receptacle, Three Pole, 30A Hubbellock, 3 Phase 600V AC, Terminal Screws, Gray.

Performance

- 600V RMS - Electrical - Operations
- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V minimum
- Electrical - Environmental - Max. Working Voltage
- External fully adjustable feet - Mechanical - Product Identification
- Identification and ratings are part of external label and receptacle face - Mechanical - Terminal Identification
- In accordance with UL 746C - Mechanical - Mounting
- In accordance with UL, CSA and international conventions - Environmental - Flammability
- IP54 suitability - Environmental - Operating Temperature
- Maximum continuous +75°C Minimum continuous -40°C - Environmental - UV Resistance
- Mechanical 10,000 cycles
- Electrical 6,000 cycles - Mechanical - Impact Resistance
- UL94 - 5 VA and VO classification - Environmental - Moisture Resistance

General

Catalog Number	SEHBL3
Color	Gray
EU RoHS Indicator	No
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Base - PBT• Conduit Hub - Zinc 3/4" watertight

- Enclosure Gasket - Neoprene
 - Handle - PBT
 - Shaft - PBT
 - Top - PBT
- For Hubbellock devices
Switched Enclosure
783585006000

Style
Type
UPC

Dimensions

Weight 3.8 lb

Electrical Ratings

Dielectric Strength Withstands 3,000V minimum

Conductor Related

Wire Size #10 AWG

Certifications And Compliance

- Industry Standard(s)
- CSA Certified Type 3R and 12K Enclosure Rating
 - Listed to UL Standard

Logistics

Carton Quantity 1

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - SEHBL3](#)
[Warranty - Industrial & Commercial Products](#)