

## Straight Blade Devices, Receptacles, Duplex, SNAPConnect, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Nylon, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAP5262IA](#)



Straight Blade Devices, Receptacles, Duplex, SNAPConnect, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Nylon, Ivory

### Application

Extra Heavy Duty Specification Grade

### Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification Ratings are a permanent part of the device
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

### General

Catalog Number	SNAP5262IA
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Finder Groove Face
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Auto Self-grounding Staple - Stainless steel</li><li>• Base - PBT</li><li>• Contacts - Brass</li><li>• Face - Nylon</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Galvanized steel</li></ul>
Style	Finder Groove Face
Type	Standard Duplex
UPC	783585247816

### Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Connectorized
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

### Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-15R

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - SNAP5262IA](#)



**A Hubbell brand**