

Switches, Single Pole  
15A, 120-277V AC

## HBL® Extra Heavy Duty Industrial Locking Switch

# HUBBELL

### Features

- Large brass binding head screws with deep slots
- Lock circuits On or Off
- Strip gauge for accurate wiring

### Ordering Information

Description	Color	UPC	Catalog Number
Key Guide,back and side wired	Gray	783585188454	HBL1201LG

### Listings

UL Listed  
CSA Certified  
Fed. Spec. W-S-896

### Specifications

Top Material	Thermoset
Base Material	Thermoset, Blue
Key Guide	Metallic, Gray
Contacts	Silver Alloy
Terminal Screws	Brass
Ground Screw	Brass (Green)

### Performance

#### Electrical


Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	15A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

#### Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper wire only

#### Environmental

Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact



### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

