

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Commercial Specification Grade Duplex
Receptacles for Controlled Applicatoins



Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Half-Controlled receptacle with one face marked and the circuit tab removed
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load Logic control's or any available energy management system

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Smooth face, back and side wired.	Light Almond	783585551050	BR15C1LA

Listings


NEMA® WD-6 Compliant
UL Listed to UL498 File No. E2186
CSA Certified 22.2, No. 42
Fed. Spec. W-C-596

Specifications

Face	Nylon
Base	Nylon
Wire Clamp	.062 in. (1.6) Nickel plated steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Galvanized Steel
Power Contacts	.030 in. (.8) Brass
Ground Contacts	Brass
Terminal Screws	Plated steel
Mounting Strap	.040 in. (1) Galvanized steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG stranded or solid copper wire only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Online Resources

eCatalog

