

Temporary Power

Temporary Industrial Lighting

LED Stringer Lights

HUBBELL

Features

- Self Locking Connector
- Magnetic mounting bracket
- Bracket Adjustment Knobs
- Hanging hook
- For Wet Locations

Ordering Information

Description	UPC	Catalog Number
60 LEDs per fixture, light string with magnetic base included	783585580197	HBL182S20LEDH



Listings

UL
CSA
ETL

Online Resources

eCatalog

Specifications

Product Type	LED
Plug Type	NEMA 1-15P
Connector Type	NEMA 1-15R

Performance

Electrical	
Lamp Life	50,000 Hours
Lumen Output per Fixture	1,100
Rating	15A 120VAC 60Hz.
Watt per fixture	9.6

Mechanical	
Cord	18/2 18 AWG
Cord Length	20 ft. 18 AWG
Enclosure	Polycarbonate
Lens	Polycarbonate
Lens Gasket	Silicon
Mounting Bracket/Hanging Hook	Steel
Number of fixtures	1

