Twist-Lock® Devices 20A, 125V AC, 2 Pole, 3 Wire Grounding Safety-Shroud® Receptacle

HUBBELL

Features

- Accepts Hubbell shrouded and standard NEMA locking plugs
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Engineered thermoplastic housing is impact and corrosion resistant, making it suitable for heavy-duty industrial environments

Ordering Information

Description **Device Color UPC** Catalog Number RPT angle housing, 783585234007 HBL2310AR Gray one gang.

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Flange Gray RPT Terminal Retainer Clear polycarbonate **Body Contact Carrier** Natural (white) nylon **Body Holding Screws** Steel, zinc plated Contacts **Brass** Mounting Plate Steel, zinc plated

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage

Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability V2 or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)







Accessories

HBL2311S Plug

Resources

Customer Use Drawing eCatalog

