

Floor Boxes

Flush Round Concrete Floorboxes

1-Gang/ Single Service

HUBBELL

Features

- Typically used in 2nd Floor and Above Concrete Floors
- Pregalvanized Stamped Steel Box
- (6) 3/4", 1", 1-1/4" Concentric Knockouts
- 4.00" minimum depth of pour
- 1.25" prepour and 0.50" post pour adjustment

Ordering Information

| Cover Style | Box Type | UPC | Catalog Number |
|-------------|-------------|--------------|----------------|
| Round | Above Grade | 783585695983 | FB2527 |

Listings

cULus Listed
UL 514A Listed
CSA C22.2 No 18 certificated

Specifications

| | |
|--------------------------|--|
| Box Base Material | Cast Iron |
| Box Top Material | Stamped Steel |
| Box Finish | Green Powder Paint |
| Concrete Cover | Tin Plate |
| Cover Frame Material | Stamped Steel |
| Device Chamber Grounding | 6" Long #12 AWG Solid Copper Wire |
| Low Voltage Divider | NA |
| Wiring Chamber Volumes | 30.0 IN ³ [491.7CM ³] |

Performance

| Mechanical | |
|-------------------------------------|----------------------|
| Box Height | 3.80" [96.4mm] |
| Box Length | 6.00" [152.4mm] |
| Box Width | 4.85" [123.2mm] |
| Concrete Pour- Minimum Depth | 3.00" [76.2mm] |
| Concrete Pour- Post Pour Adjustment | .50" [12.7mm] |
| Knockouts – Bottom | (2) 3/4", 1", 1-1/4" |
| Knockouts – Ends | (2) 3/4", 1", 1-1/4" |
| Threaded Hubs | (4) 3/4" |



Related Products

| | |
|------------------------|--------|
| Brass Cover Flange | S5016 |
| Aluminum Cover Flange | SA5016 |
| Brass Carpet Flange | S3082 |
| Aluminum Carpet Flange | SA3082 |

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

