

**Industrial Grade Extra Heavy Duty Ground Fault Receptacle  
Autoguard Self-Test GFCI  
20A, Tamper-Resistant, Weather-Resistant**

# HUBBELL

## Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

## Ordering Information

Description	Color	UPC	Catalog Number
20A, 125V, Style Line, AUTOGUARD self test GFCI receptacle, tamper-resistant and weather-resistant, flush face, back and side wired	White	783585745985	GFSG5362W

## Listings

UL Listed - Canadian and U.S.  
Meets ADA Standard  
Meets NEC requirements  
CSA Certified  
Fed Spec  
NEMA WD-6 Complaint

## Specifications

Face	PC/PBT
Base	Nylon
Power Contacts	Nickel Plated Brass
Ground Contacts	Nickel Plated Brass
Mounting Strap	Nickel Plated Brass
Mounting Screw	Stainless Steel

## Performance

### Construction

Grounding	Autoground Clip
Terminal	#14 to #10AWG
Termination	Back and Side

### Electrical

Dielectric	Withstand 1,500V
Feed-through	20 Amp Protection
Flammability	V0 per UL 94
Frequency	60 Hz
Operating Temp	-35 C to 66 C
Short Circuit	10,000 Amps
Trip Level	4 mA to 6mA (0.025 sec)
Voltage	120V AC (-15%, +10%)

### Electrical Ratings

Amperage	20A
----------	-----



## Related Products

Accessories

(1) Matching Nylon and (1) Stainless Steel Wall Plate Included

## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

