

Twist-Lock® Devices
30A, 125/250 AC, 3 Pole, # Wire Non-Grounding
Insulgrip® Flanged Inlet

HUBBELL

Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|--------------------------|--------------|-----|----------------|
| Nylon casing, back wired | White | | HBL2665 |

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-------------------|-----------------------------------------------|
| Housing | Nylon |
| Terminal Retainer | Clear polycarbonate |
| Blades | Brass |
| Terminal Screws | #10-32 Brass (Phillips / Slotted / Robertson) |
| Terminal Clamp | Cold rolled steel – nickel plated |
| Assembly Screws | Steel - nickel plated |
| Mounting Screw | Nickel plated brass |

Performance

| | |
|-------------------------|----------------------------------------------------------|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Terminal Accommodation | #16 AWG - #8 AWG solid or stranded copper wire only. |
| Terminal Identification | Terminals identified in accordance with UL 498 |
| Environmental | |
| Flammability | HB or better per UL94/CSA 22.2 No.0.17 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C. Minimum -40°C (w/o impact) |



Accessories

| | |
|-------------------------|---------|
| Connector | HBL2663 |
| Weatherproof Lift Cover | WP2 |

Resources

| |
|----------|
| eCatalog |
|----------|

