

Industrial Grade Extra Heavy Duty Ground Fault Receptacle

Autoguard Self-Test GFCI

15A, Hospital Grade, Tamper-Resistant, Weather-Resistant

Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

Ordering Information

Description	Color	UPC	Catalog Number
15A, 125V, Style Line, AUTOGUARD self test GFCI receptacle, hospital grade, tamper-resistant and weather-resistant, flush face, back and side wired	White	783585746043	GFSG8200W

Listings

UL Listed - Canadian and U.S.
Meets ADA Standard
Meets NEC requirements
CSA Certified
Fed Spec
NEMA WD-6 Complaint

Specifications

Face	PC/PBT
Base	Nylon
Power Contacts	Nickel Plated Brass
Ground Contacts	Nickel Plated Brass
Mounting Strap	Nickel Plated Brass
Mounting Screw	Stainless Steel

Performance

Construction

Grounding	Autoground Clip
Terminal	#14 to #10AWG
Termination	Back and Side

Electrical

Dielectric	Withstand 1,500V
Feed-through	20 Amp Protection
Flammability	V0 per UL 94
Frequency	60 Hz
Operating Temp	-35 C to 66 C
Short Circuit	10,000 Amps
Trip Level	4 mA to 6mA (0.025 sec)
Voltage	120V AC (-15%, +10%)

Electrical Ratings

Amperage	15A
----------	-----

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

HUBBELL



Related Products

Accessories

(1) Matching Nylon and (1) Stainless Steel Wall Plate Included

Online Resources

Customer Sales Drawings

eCatalog

Installation Instructions

