

# Ground Fault Products

## Commercial Tamper-Resistant GFCI Receptacles

# HUBBELL

### Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Alarm version provides audible notification of a trip condition
- Triple wipe construction

### Ordering Information

Description	Catalog Number	UPC	Color
15A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, alarm, tamper-resistant, flush face,	GFTRST15WB	883778228230	GFTRST15WB



### Listings

UL Listed - Canadian and U.S.  
Meets ADA Standards  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

### Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel

### Performance

#### Electrical

Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)

#### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

#### Environmental

Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F

### Accessories

Wallplates for duplex openings

### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

