

Ground Fault Products

Commercial Tamper-Resistant GFCI Receptacles

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Alarm version provides audible notification of a trip condition
- Triple wipe construction

Ordering Information

Description	Catalog Number	UPC	Color
15A, 125V, Style Line®, hospital grade, AUTOGUARD® self test GFCI receptacle,	GFTRST82GYB	783585534183	GFTRST82GYB

Listings

UL Listed - Canadian and U.S.
Meets ADA Standards
Meets all NEC® requirements
CSA Certified
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Brass
Mounting Screws	Zinc plated steel


Performance

Electrical	
Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)

Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental	
Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F

HUBBELL



Accessories

Wallplates for duplex openings

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

