

IEC Pin and Sleeve

100A, 240V, 2 Pole, 3 Wire

Mechanical Interlock

Features

- Plug cannot be removed until the switch is turned off.
- Large gears enclosed in a gear box to ensure reliable switching.
- Lockable handle to meet OSHA Lockout/Tagout regulations.
- Pre-wired IEC Pin and Sleeve receptacle
- Enclosure Type 4X, 12 and IP67 Suitability

Ordering Information

| Description | UPC | Catalog Number |
|---|--------------|----------------|
| Circuit-Lock® Pin and Sleeve Mechanical Interlock | 783585405803 | HBL3100MI6W |

Color code

Blue

Standards

UL Listed
CSA Certified

Specifications

| | |
|------------------|----------|
| Face | Valox® |
| Base | Valox® |
| Enclosure Gasket | Neoprene |
| Shaft Seal | Neoprene |
| Conduit Hub | Zinc |

Performance

| Electrical | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current and voltage |
| Dielectric Voltage | Withstands 3,000V AC Min |
| Max. Working Voltage | 600V AC RMS |

Mechanical

| | |
|-------------------------|--|
| Impact Resistance | In accordance with UL 746C |
| Mounting | External adjustable feet |
| Product Identification | Identification and ratings are part of the external label and molded into the receptacle mount |
| Terminal Identification | In accordance with UL, CSA and international conventions |


Environmental

| | |
|-----------------------|---|
| Flammability | UL94-5VA and V-0 Classification |
| Ingress Protection | IP67 Suitability |
| Moisture Resistance | Outdoor - 4X (Watertight, Washdown); Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids). |
| Operating Temperature | Max. Continuous +75°C; Min. Continuous -40°C |

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

HUBBELL



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

