UL 1686 C1 Pin and Sleeve

100A, 600/250V AC/DC, 2 Pole, 3 Wire

Reversed Service Insulgrip® Receptacle

Features

- Closure cap with neoprene gasket provides a 4X watertight seal while not in use
- All brass sleeve contacts provide reliable electrical contact with mating pins
- O-Rings provide a watertight and dust tight seal around sleeves negating contamination to the wire chamber
- Catalog number and rating are visible while in use, color coded for Style 1 or Style 2



Description Watertight Insulgrip **UPC** 783585012056

Catalog Number HBL3100RS2WR

Receptacle, Reversed Service

Grounding Style

Style 2



Device Color

Aluminum

UL Standard 1682

CSA Certified to CSA Spec. C22.2 No. 182.1 UL Listed and CSA Certified Type 4X

Specifications

Housing

Gaskets & Seals

Contact Carrier

Pin Spring Cover **Epoxy Painted Aluminum**

Neoprene

Thermoset Polyester Beryllium Copper

Epoxy Painted Aluminum

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Max. Working Voltage Withstands 3,000V AC

600V AC RMS

Mechanical

Impact Resistance Per CSA C22.2, No. 182.1, UL 1682

Product Identification Identification and ratings are permanently fastened

to the device housing

Terminals identified in accordance with UL 1686(1,

2, 3, Green)

Environmental

Terminal Identification

Flammability (Enclosure) UL 94V-0 and CSA C22.2 No. 0.17

Moisture Resistance Type 3, 4, 4X per UL 50E and CSA 22.2, No. 94
Operating Temperatures Max. Continuous 75°C; Min. -40°C w/o impact -25°

with impact

Online Resources

Customer Use Drawing

eCatalog

Installation Instructions



HUBBELL





