

Twist-Lock® Devices
15A, 250V, 2 Pole, 3 Wire Grounding
Insulgrip® Plug

Features

- Individually molded face for each blade configuration
- Roomy wiring chamber provides ample space for wiring
- Ribbed nylon housing provides a secure grip that's impact and chemical resistant

Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|--|------------------------|--------------|----------------|
| Insulgrip® plug, corrosion resistant, yellow and white nylon | .230"-.720" (5.8-18.3) | 783585160009 | HBL45CM70C |

Listings


Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|----------------------|---|
| Housing / Cord Clamp | Nylon |
| Terminal Retainer | Clear polycarbonate |
| Blades | Nickel Plated Brass |
| Terminal Screws | #8-32 Bronze (Phillips / Slotted / Robertson) |
| Terminal Clamp | Cold rolled steel – nickel plated |
| Assembly Screws | Stainless Steel |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Terminal Accommodation | #18 AWG - #10 AWG stranded copper wire only. |
| Terminal Identification | Terminals identified in accordance with UL 498 |
| Environmental | |
| Flammability | HB or better per UL94 or CSA 22.2 No. 0.6 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C Minimum -40°C (w/o impact) |



Accessories

| | |
|-------------------|------------|
| Connector | HBL45CM79C |
| Weatherproof Boot | HBL60CM23 |

Resources

Customer Use Drawing
eCatalog

