

Twist-Lock® Devices
15A, 250V, 2 Pole, 3 Wire Grounding
Insulgrip® Connector

HUBBELL

Features

- Ribbed nylon housing provides secure, impact and chemical resistant grip
- Superior cord grip design protects terminations from excess strain
- Integral VARI-SIZE insert accomodates a wide range of cord diameters

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Corrosion resistant, yellow and white nylon.	.230"- .720" (5.8-18.3)	783585160108	HBL45CM79C

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications


Housing / Cord Clamp	Nylon
Terminal Retainer	Clear polycarbonate
Contacts	Nickel plated brass
Terminal Screws	#8-32 Nickel plated copper alloy (Phillips / Slotted / Robertson)
Terminal Clamp	Cold rolled steel – nickel plated
Assembly Screws	Stainless Steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Accommodation	#18 AWG - #8 AWG stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94 or CSA 22.2 No. 0.6
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C Minimum -40°C (w/o impact)



15A 250V
NEMA L6-15R
UL/CSA



Accessories

Plug	HBL45CM70C
Weatherproof Boot	HBL60CM24

Resources

Customer Use Drawing
eCatalog

