

Temporary Power
Temporary Industrial Lighting
A Type Twist-Lock® and Straight Blade
Light Strings

HUBBELL

Ordering Information

Description	UPC	Catalog Number
Straight Blade light string; metal guards	783585528250	HBL123S50MS

Listings

UL
CSA
ETL

Specifications

Plug Type	NEMA 5-15P
-----------	------------

Performance

Electrical	
Max Watts per Fixture	150
Rating	15A 125V
Mechanical	
Cord Length	50 ft.
Cord Type	12/3 STW
Number of fixtures	5



Online Resources

eCatalog
