

Straight Blade Devices 15A, 277V AC, 2 Pole, 3 Wire Grounding Connector Body

HUBBELL

Features

- Classic body design
- External cord clamp

Resources

[eCatalog](#)

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Connector Body, phenolic and steel body	.296"-.625"(7.5-15.9)	783585013374	HBL5324

Listings

UL Listed to UL498 File E1706
CSA Certified to C22.2 No. 42 File 280C
NEMA® WD-6 Compliant

Specifications

Body	Phenolic
Contacts	.031 in. Brass
Terminal Screws	Brass
Cord Clamp	Plated steel
Assembly Screws	Nickel plated steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG stranded copper wire only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 V-1 or better
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

