Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

HBL® Extra Heavy Duty MAX Specification Grade **Duplex Receptacles**

Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face
- Corrosion resistant

Ordering Information

Description Corrosion resistant, deep body design with circuit ID face. Back and side wired.

Device Color Yellow

UPC Number 783585411064

Catalog Number HBL53CM62

Listings

UL Listed to UL498 File No. E2186 Certified to CSA 22.2, No. 42 File 285

Fed. Spec. WC596 **NEMA® WD-6 Compliant**

Specifications

Face

Rase

By-Pass Power Contacts .036". (.9) Nickel plated brass

Ground Contacts Clamping Plate **Terminal Screws**

Mounting Strap .050 in. (1.3) Nickel plated brass

Automatic Self-grounding Clip Mounting Screws Stainless steel

Plated brass

Nylon PBT

Stainless steel

.031 in. (.8) Brass

Nickel plated brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #12-#10 AWG copper stranded or solid

conductor only

Terminals identified in accordance with UL 498

and CSA

Environmental

Terminal Identification

Top: UL 94V-2, Base: UL 94V-0 Flammability


Maximum continuous 75°C; minimum -40°C (w/o **Operating Temperatures**

impact)

HUBBELL







Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

Online Resources

Customer Sales Drawings

eCatalog

Installation Instructions

