Twist-Lock® Devices 15A, 277V AC, 2 Pole, 3 Wire Grounding Stainless Steel Flanged Receptacle



Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

-			
Description	Device Color	UPC	Catalog Number
Stainless steel casing,	Brown/Stainless	783585236971	HBL4785
brown phenolic			

Listings

Listed to UL 498 Fed. Spec. W-C-596 Certified to CSA C22.2 No.42


Specifications

Flange	Stainless steel
Blades	Brass
Terminal Screws	Brass
Mounting Screw	Nickel plated brass

Performance

Electrical Current Interrupting Dielectric Voltage	Certified for current interrupting at full rated current Withstands 2,000V minimum
Mechanical Terminal Accommodation	#18 AWG - #10 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental Flammability Moisture Resistance Operating Temperatures	HB or better per UL94/CSA 22.2 No.0.17 IP20 Suitability Maximum Continuous 75°C; Minimum -40°C (w/o impact)





Accessories

Plug	HBL4770C

Resources

15A 277V AC NEMA L7-15R

UL/CSA 2 HP

	Customer Use Drawing	
eCatalog	eCatalog	

