

Midget Twist-Lock® Devices  
 15A, 125V AC, 2 Pole, 2 Wire Non-Grounding  
 Flanged Inlet

# HUBBELL

## Features

- Stainless Steel mounting flange
- High heat resistant phenolic base



## Ordering Information

Description	Terminals	UPC	Catalog Number
Stainless steel flanged inlet.	Exposed	783585237329	HBL7467

## Listings

Listed to UL 498

## Specifications

Flange	Stainless Steel
Base	Phenolic
Blades	Brass
Terminal Screws	#5-40 Brass

## Performance

### Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Terminal Accommodation	#18 AWG - #14 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498

### Environmental

Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



## Accessories

Valise® Connector	HBL7464V
-------------------	----------

## Resources

Customer Use Drawing  
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

