

Non-NEMA Twist-Lock® Devices  
10A, 250V, 15A, 125V, 3 Pole, 3 Wire  
Non-Grounding  
Stainless Steel Flanged Inlet

# HUBBELL

## Features

- Heat resistant thermoset construction
- Stainless steel casing
- #5-40 terminal screws
- Mounting screws included

## Ordering Information

Description	Device Color	UPC	Catalog Number
Stainless steel casing, brown phenolic	Brown/Stainless	783585237640	HBL7556



## Accessories

Connector	HBL7565C
-----------	----------

## Resources

[eCatalog](#)

## Specifications

Flange	Stainless steel
Blades	Brass
Terminal Screws	Brass
Mounting Screw	Nickel plated brass

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Terminal Accommodation #16 AWG - #12 AWG solid or stranded copper wire only

Terminal Identification Terminals identified in accordance with UL 498

### Environmental

Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

