

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

HBL<sup>®</sup> Extra Heavy Duty MAX Specification Grade Duplex Receptacles

- Features
- Back wired ground terminal allows faster, easier installation
  - One-piece brass integral ground strap
  - Finder Groove Face
  - Deep body design with circuit ID face
  - Corrosion resistant

Ordering Information

| Description  | Device Color | UPC Number   | Catalog Number |
|--|--------------|--------------|----------------|
| Corrosion resistant, deep body design with circuit ID face. Back and side wired. | Ivory        | 783585411026 | HBL52CM62I     |

Listings

UL Listed to UL498 File No. E2186  
Certified to CSA 22.2, No. 42 File 285  
Fed. Spec. WC596  
NEMA<sup>®</sup> WD-6 Compliant

Specifications

|                               |                                    |
|-------------------------------|------------------------------------|
| Face                          | Nylon                              |
| Base                          | PBT                                |
| By-Pass Power Contacts        | .036". (.9) Nickel plated brass    |
| Ground Contacts               | .031 in. (.8) Brass                |
| Clamping Plate                | Nickel plated brass                |
| Terminal Screws               | Plated brass                       |
| Mounting Strap                | .050 in. (1.3) Nickel plated brass |
| Automatic Self-grounding Clip | Stainless steel                    |
| Mounting Screws               | Stainless steel                    |



Performance

| Electrical              |  |
|-------------------------|--|
| Current Interrupting    | Certified for current interrupting at full rated current |
| Dielectric Voltage      | Withstands 2,000V minimum                                |
| Mechanical              |  |
| Product Identification  | Ratings are a permanent part of the device               |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only      |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA   |
| Environmental           |  |
| Flammability            | Top: UL 94V-2, Base: UL 94V-0                            |
| Operating Temperatures  | Maximum continuous 75°C; minimum -40°C (w/o impact)      |

HUBBELL



15A 125V AC  
NEMA 5-15R  
UL CSA  
0.5 HP



Complementary Products

Wallplate or Weatherproof Cover      Duplex Opening

Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

