

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

HBL[®] Extra Heavy Duty MAX Hospital Grade Duplex Receptacle

HUBBELL

Features

- Slender/compact design
- Impact-resistant finder groove face
- Triple wipe contacts
- Entire face illuminated by two LEDs

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|--|--------------|--------------|----------------|
| Illuminated face, back and side wired. | White | 783585016474 | HBL8200ILW |

Listings

UL Listed to UL498 File No. E2186
CSA Certified
Fed. Spec. W-C-596
NEMA[®] WD-6 Compliant

Specifications


| | |
|-------------------------------|------------------------------------|
| Face | Polycarbonate |
| Base | PBT |
| By-Pass Power Contacts | .036". (.9) Nickel plated brass |
| Ground Contacts | .031 in. (.8) Brass |
| Clamp | Nickel plated steel |
| Terminal Screws | Brass |
| Mounting Strap | Brass |
| Automatic Self-grounding Clip | .050 in. (1.3) Nickel plated brass |
| Mounting Screws | Stainless Steel |

Performance

| Electrical | |
|-------------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #14-#10 AWG stranded or solid copper wire only |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |
| Environmental | |
| Flammability | UL 94V-2 |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



15A 125V AC
NEMA 5-15R
UL CSA
0.5 HP



Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

