Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

Heavy Duty, Specification Grade Tamper-Resistant Duplex Receptacles

HUBBELL

Features

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Brass mounting strap and Triple Wipe contacts
- High impact resistant face with circuit I.D. marking area
- Complies with National Electrical Code (NEC®) requirements for Tamper Resistant receptacles

Ordering Information

DescriptionFed-Spec listed, Smooth nylon face, back and side wired, duplex

Device Color Black **UPC Number** 783585542478

Catalog Number HBL5362BKTR


Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Nylon Base PBT **Power Contacts Brass Ground Contact** Brass Clamping Plate Plated steel Mounting Strap Brass Automatic Self-grounding Staple Stainless steel Mounting Screws Zinc plated steel





Complementary Products

Wallplate or Weatherproof Cover

Duplex Opening

Performance

Dielectric Voltage

Electrical

Current Interrupting Certified for current interrupting at full rated

current

Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #12-10 AWG stranded or solid copper wire only.
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C; minimum -40°C (w/o

impact)

Online Resources

Customer Sales Drawings

eCatalog

Installation Instructions

