

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

HBL<sup>®</sup> Extra Heavy Duty MAX, Specification Grade, Duplex Receptacle

Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face
- Bulk Packed

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Non-isolated ground, bulk pack of 100.	Orange	783585000497	HBL5362M4

Listings

Certified to CSA 22.2, No. 42 File 285  
NEMA® WD-6 Compliant  
UL Listed to UL498 File E2186  
Fed. Spec. W-C-596

Specifications

Face	Nylon
Base	PBT
By-Pass Power Contacts	.036" (.9) Brass
Ground Contacts	.031 in. (.8) Brass
Clamping Plate	Nickel plated brass
Terminal Screws	Plated brass
Mounting Strap	.050 in. (1.3) Brass
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Zinc plated steel


Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	Top: UL 94V-2, Base: UL 94V-0
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

HUBBELL



20A 125V  
NEMA 5-20R  
UL CSA  
1 HP



Complementary Products

Wallplate or Weatherproof Cover      Duplex Opening

Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

