

Switched Disconnects and Enclosures

Unfused Hazardous Location Disconnect Switches

30 Amp, 3 Pole

HUBBELL

Features

- Copper-free aluminum construction with electrostatically applied polyester/epoxy finish to prevent corrosion
- Compact NEMA 4X enclosure and footprint allows easy installation in tight locations
- Gasketed flange with O-ring located inside bolt circle to seal out moisture
- Lockable handle to meet OSHA Lockout/Tagout regulations. Large visible rotary handle with “ON-OFF” indicator allows a quick means of disconnecting power
- Disconnects contain UL98 certified switch



Ordering Information

Description	UPC Number	Catalog Number
30A 3-Pole Disconnect Switch	783585242590	HBLB7NFD13A

Online Resources

[eCatalog](#)
[Installation Instructions](#)

Listings

Class I, Div. 1 & 2, Groups B, C, D
Class I, Zones 1 & 2, Groups IIB+ H2, IIA
Class II, Div. 1 & 2, Groups E, F, G
Class III, NEMA 3, 4, 4X, 7(B,C,D), 9(E,F,G)

Specifications

Enclosure Material	Copper-free aluminum
Cover Bolts	316 Stainless Steel
O-Ring Gasket	Silicone
Finish	Grey Powder Polyester painted exterior, electrostatically applied

Performance

Electrical

Max. Working Voltage 600V AC

Mechanical

Conduit Size 1 NPT
Terminal Wire Size #14 AWG - #10 AWG

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

