

Switched Disconnects and Enclosures
Unfused Hazardous Location Disconnect Switches
60 Amp, 3 Pole

HUBBELL

Features

- Copper-free aluminum construction with electrostatically applied polyester/epoxy finish to prevent corrosion
- Compact NEMA 4X enclosure and footprint allows easy installation in tight locations
- Gasketed flange with O-ring located inside bolt circle to seal out moisture
- Lockable handle to meet OSHA Lockout/Tagout regulations. Large visible rotary handle with "ON-OFF" indicator allows a quick means of disconnecting power
- Disconnects contain UL98 certified switch



Ordering Information

| Description | UPC Number | Catalog Number |
|---|--------------|----------------|
| 60A 3-Pole Disconnect Switch with Auxiliary Contact | 783585242637 | HBLB7NFD26AA |

Online Resources

[eCatalog](#)
[Installation Instructions](#)

Listings

Class I, Div. 1 & 2, Groups B, C, D
Class I, Zones 1 & 2, Groups IIB+ H2, IIA
Class II, Div. 1 & 2, Groups E, F, G
Class III, NEMA 3, 4, 4X, 7(B,C,D), 9(E,F,G)

Specifications

| | |
|--------------------|---|
| Enclosure Material | Copper-free aluminum |
| Cover Bolts | 316 Stainless Steel |
| O-Ring Gasket | Silicone |
| Finish | Grey Powder Polyester painted exterior, electrostatically applied |

Performance

| | |
|----------------------|-----------------|
| Electrical | |
| Max. Working Voltage | 600V AC |
| Mechanical | |
| Conduit Size | 1½ NPT |
| Terminal Wire Size | #8 AWG - #1 AWG |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

