

## Switched Disconnects and Enclosures

### Unfused Hazardous Location Disconnect Switches

#### 60 Amp, 3 Pole

# HUBBELL

#### Features

- Copper-free aluminum construction with electrostatically applied polyester/epoxy finish to prevent corrosion
- Compact NEMA 4X enclosure and footprint allows easy installation in tight locations
- Gasketed flange with O-ring located inside bolt circle to seal out moisture
- Lockable handle to meet OSHA Lockout/Tagout regulations. Large visible rotary handle with "ON-OFF" indicator allows a quick means of disconnecting power
- Disconnects contain UL98 certified switch



#### Ordering Information

Description	UPC Number	Catalog Number
60A 3-Pole Disconnect Switch	783585242606	HBLB7NFD26A

#### Online Resources

[eCatalog](#)  
[Installation Instructions](#)

#### Listings

Class I, Div. 1 & 2, Groups B, C, D  
Class I, Zones 1 & 2, Groups IIB+ H2, IIA  
Class II, Div. 1 & 2, Groups E, F, G  
Class III, NEMA 3, 4, 4X, 7(B,C,D), 9(E,F,G)

#### Specifications

Enclosure Material	Copper-free aluminum
Cover Bolts	316 Stainless Steel
O-Ring Gasket	Silicone
Finish	Grey Powder Polyester painted exterior, electrostatically applied

#### Performance

<b>Electrical</b>	
Max. Working Voltage	600V AC
<b>Mechanical</b>	
Conduit Size	1½ NPT
Terminal Wire Size	#14 AWG - #4 AWG

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

