

IEC Pin and Sleeve
Accessories
Ground Block

HUBBELL

Ordering Information

Description 60/100A replacement ground block	UPC 783585955162	Catalog Number HBL60100RGB
--	----------------------------	--------------------------------------

Product Type
Replacement Ground Block

Standards

UL Listed
CSA Certified

Specifications

Hinge Spring	Stainless Steel
Assembly Screws	Stainless Steel
Gaskets	Neoprene
Interlock Items	Replacement Parts

Performance

Electrical
Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstand 3,000V AC
Max Working Voltage 600V AC RMS

Mechanical
Impact Resistance In accordance with UL746C
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount.
Terminal Identification Terminals identified in accordance with North American and International conventions

Environmental
Flammability UL94-5VA and V-0 classification
Ingress Protection IP67 Suitability
Operating Temperatures Max Continuous- 75 °C, Minimum -40 ° w/o Impact

Online Resources

eCatalog



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

