Non-NEMA Twist-Lock® Devices 20A, 125/250V, 3 Pole, 3 Wire Non-Grounding Insulgrip® Connector



Features

- · Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Corrosion resistant,	.360"930" (9-24)	783585037530	HBL73CM14C
yellow nylon.	,		



Accessories

Plug	HBL996CM5C
Weatherproof Boot	HBL60CM32
Flanged Inlet	HBL3325C
Weatherproof Boot	HBL6031

Resources

eCatalog

Specifications

Terminal Retainer

Housing / Cord Clamp Nylon

Contacts **Brass**

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Clear polycarbonate

Cold rolled steel - nickel plated **Terminal Clamp**

Assembly Screws Steel - zinc plated

Performance

Electrical

Certified for current interrupting at full rated current **Current Interrupting** Dielectric Voltage

Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94 or CSA 22.2 No. 0.7

Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)

