# Midget Twist-Lock® Devices 15A, 125V AC, 2 Pole, 3 Wire Grounding Flanged Inlet



- Stainless Steel mounting flange
- High heat resistant phenolic base

## **Ordering Information**

DescriptionTerminalsUPCCatalog NumberStainless steel flangedExposed783585237794HBL7595inlet.Inlet.Inlet.Inlet.Inlet.	-			
	Description	Terminals	UPC	Catalog Number
	0	Exposed	783585237794	HBL7595

#### Listings

Listed to UL 498 Certified to CSA C22.2 No.42

### **Specifications**

Flange	Stainless Steel
Base	Phenolic
Blades	Brass
Terminal Screws	#5-40 Brass

## Performance

Electrical Current Interrupting Dielectric Voltage	Certified for current interrupting at full rated current Withstands 2,000V minimum
Mechanical Terminal Accommodation	#18 AWG - #14 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
<b>Environmental</b> Flammability Moisture Resistance Operating Temperatures	HB or better per UL94/CSA 22.2 No.0.17 IP20 Suitability Maximum Continuous 75°C; Minimum -40°C (w/o impact)

## Accessories

15A 125V NEMA ML-2P

Valise® Connector	HBL7593V	
Connector	HBL77593	
Angled Connector	HBL7571	

#### Resources

Customer Use Drawing eCatalog



Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.





