


HUBBELL-PRO LOCKING CONNECTOR

KEY FEATURES:

- Impact modified nylon body construction
- Rubber dust shield
- NEMA configuration and rating marked on device face
- Ready-to-wire
- Clearly marked terminal identification



DIMENSIONS



LISTINGS

- UL Standard 498
- CSA Standard C22.2 No. 42-M1984
- CSA Standard C22.2 No. 182.2-M1987
- Fed Spec WC596
- RoHS Compliant

CORD RANGE

- 5 Conductor (stranded copper wire only)
- #14/5 SO - #8/5 SO
.625 in. - 1.050 in. (15.9 mm - 26.7 mm)

PERFORMANCE

- Flammability: V-0
- Operating Temperature:
 - Max. continuous 60°C;
 - Min. -40°C without impact

ENVIRONMENTAL

- NEMA Type 1
- IP20

MATERIALS

| Part | Description |
|----------------|-----------------------------|
| Pull Down Ring | Nylon, black |
| Grip Body | Nylon, black |
| Terminal Cover | Lexan |
| Drive Screw | Steel, Zinc Plate |
| Dust Shield | Rubber |
| Assembly Screw | Steel, Zinc Plate |
| Terminal Screw | Steel, Green, Nickel, Brass |
| Wire Clamp Nut | Brass/Steel/Tin Plate |
| Contacts | Brass |
| Connector face | Nylon, White |

ACCESSORIES

- Weather protective boot **HBC2**

| NEMA No. | Config. | Rating | Pole/Wire | Catalog Number |
|----------|---------|------------------------|--------------------|----------------|
| L21-20R | | 20A 3ØY 120/208V AC | 4P 5W Grounding | L2120C |
| L22-20R | | 20A 3ØY 277/480V AC | 4P 5W Grounding | L2220C |
| L23-20R | | 20A 3ØY 347/600V AC | 4P 5W Grounding | L2320C |
| L21-30R | | 30A 3ØY 120/208V AC | 4P 5W Grounding | L2130C |
| L22-30R | | 30A 3ØY 277/480V AC | 4P 5W Grounding | L2230C |
| L23-30R | | 30A 3ØY 347/600V AC | 4P 5W Grounding | L2330C |